

High Power Class B Amplifier

LC552 DATA SHEET

FEATURES

- operates over a supply range of 1.0 V to 3.0 V
- selectable class B or vari-bias class A operation
- feedback stabilized gain ≤ 80 dB
- high power output > 140 dBSPL
- independent preamplifier and output modules
- · minimum external parts count

STANDARD PACKAGING


- 14 pin DIP
- 14 pin SOIC
- Chip (50 x 52 mils)

DESCRIPTION

The LC552 is a versatile low voltage, high gain, high power output amplifier.

It features a preamplifier module with adjustable gain and a unique power amplifier module that can be operated either as a high power, high efficiency class B amplifier, with very low quiescent current consumption, or as a medium power "vari-bias" class A amplifier.

While designed specifically for use in body type hearing aids, the LC552 can be used in other applications where linear audio frequency amplification and frequency shaping is required.



All resistors in ohms, all capacitors in farads unless otherwise stated.

BLOCK DIAGRAM

Revison Date: July 1993. Document No. 500 - 58 - 6

ABSOLUTE MAXIMUM RATINGS

PIN CONNECTION


PARAMETER	VALUE / UNITS		
Supply Voltage	3 V	OUTPUT STAGE I/P ☐ ●1	14 CURRENT TRIM
Power Dissipation	200 mW	DEC A	DEC B
Operating Temperature	-10 to + 60 °C	OUTPUT A	О ООТРИТ В
Storage Temperature	-20 to + 70 °C	O/P GND	D V _{CC2}
		MIC BIAS	D V _{CC1}
CAUTION	A	PREAMP I/P	☐ FEEDBACK
CLASS 1 ESD SENSITIVITY	N	PREAMP GND 7	8 PREAMP O/P

ELECTRICAL CHARACTERISTICS

All parameters tested in Test Circuit Fig. 1.

Conditions: Supply voltage $V_B = 1.3 \text{ V DC}$, Temperature ambient = 25°C, Frequency = 1 kHz, Noise Filter Bandwidth at 12 dB/oct (0.2 to 10kHz)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Gain	A_V	Output = 0.707 VRMS	72	75	78	dB
Total Current	I _{TOT}		-	0.77	1.2	mA
Total Harmonic Distortion & Noise	THD	Output = 0.707 VRMS	-	1.5	3.0	%
Input Referred Noise			-	0.9	2.5	μV
Stable with Battery Resistance to			-	-	22	Ω
Input Impedance of Output Amplifier			18	27	36	kΩ
Frequency Response (-3 dB at 1 kHz)		Low	-	250	-	Hz
		High	-	12	-	kHz
Gain Dependence on R _B			-	0.02	-	dB/Ω



NOTES: 1. Test Circuit Amplifier Gain = 20 Log_{10} (V_O / V_I) + 40 dB

2. Preamp Gain =
$$\frac{R_F}{R_{IN}}$$
 set at 35 dB

Fig. 1 Test Circuit




Fig. 2 Functional Schematic Diagram




Fig. 3 Typical Hearing Aid Circuit

DOCUMENT IDENTIFICATION

PRODUCT PROPOSAL

This data has been compiled for market investigation purposes only, and does not constitute an offer for sale.

ADVANCE INFORMATION NOTE

This product is in development phase and specifications are subject to change without notice. Gennum reserves the right to remove the product at any time. Listing the product does not constitute an offer for sale.

PRELIMINARY DATA SHEET

The product is in a preproduction phase and specifications are subject to change without notice.

DATA SHEET

The product is in production. Gennum reserves the right to make changes at any time to improve reliability, function or design, in order to provide the best product possible.

REVISION NOTES: SOIC package added.

Gennum Corporation assumes no responsibility for the use of any circuits described herein and makes no representations that they are free from patent infringement.

© Copyright 1989 Gennum Corporation. All rights reserved. Printed in Canada.

3 500 - 58 - 6