Cermax[®] Xenon Arc Lamps

Imaging

PE1500D-10F and PE1500D-10UV CERMAX[®] FOCUSED **XENON ARC LAMPS**



Description

The Cermax® xenon arc lamp is an innovative lamp design in the specialty lighting industry. These lamps were introduced in the early 1980's and are now used in endoscopes in most major hospitals worldwide, in high brightness projection display systems, and for a wide variety of other high performance applications.

The PE1500D-10F and PE1500D-10UV Cermax® lamps have an integrated elliptical reflector, enabling high intensity, focused output of ultraviolet, visible, and infrared radiation. With their internal reflector and rugged ceramic body construction, Cermax® lamps are the safest and most compact alternative to conventional quartz xenon lamps. This makes them ideal for applications that require a high degree of illumination control. Current-regulated or power-regulated power supplies with output ripples of less than 5% are recommended. Single shot ignition

pulses are advised because radio frequency starters may damage the lamps internal reflector.

In addition to lamps, PerkinElmer Optoelectronics manufactures Cermax® arc lamp power supplies, lamp holders, OEM lighting systems, and fiber optic light sources.

Applications

- · Medical and industrial fiber optic illuminators
- Machine vision
- Infrared and visible spotlights/beacons
- Spectroscopy
- Microscopy
- · UV Curing
- · Video projection



PE1500D-10F and PE1500D-10UV

Operational Specifications

Nominal	Range	
1500 watts	900-1550 watts	
65 amps (DC)	45-80 amps (DC)	
18.5 volts (DC)	17-23 volts (DC)	
28 kilovolts (recommended minimum)		
150º C (maximum)	50º C (maximum)	
1000 hours (500 hour warranty)		
	1500 watts 65 amps (DC) 18.5 volts (DC) 28 kilovolts (recommer 150° C (maximum)	

* End of lamp life is defined as 50% of initial output.

Output at Nominal Power

F= UV Filtered Output/ UV = UV Enhanced Output


Description	PE1500D-10F	PE1500D-10UV
Radiant Output*	365 watts	-
UV Output*	19.5 watts	-
IR Output*	200 watts	-
Visible Output*	40000 Lumens	-
Color Temperature	5900 Kelvin	5050 Kelvin
Peak Instabilities	4%	4%
Spot Size at Crossover	.15" at 50% pts	.15" at 50% pts
Spot Size at Crossover	.40" at 10% pts	.40" at 10% pts

*These values indicate total output in all directions.

Wavelengths = UV<390nm, IR>770nm, Visible 390nm to 770nm.

** Beam Geometry defined as half angle at 10% PTS after 01/100/1000 hours.

Dimensions



Physical Specifications

Description
Arc Gap
Reflector Geometry
Weight
Window Diameter

Specification .075 inch (1.58 mm) Ellipsoidal $1=X^2/M^2 + Y^2/N^2$ 687 grams 1.375 inch (34.92 mm)


Focused Output Description Visible Output* **Total Output** 31000 Lumens 278 watts 12mm aperture 9mm aperture 26000 Lumens 247 watts 6mm aperture 18000 Lumens 171 watts 3mm aperture 7600 Lumens 72 watts

* Nominal values at 1500 watts after 2 hour burn-in

Notes

- Lamp must not be operated with window facing upwards within 45° of vertical.
- 2. Seal temperature must not exceed 150° C.
- **3.** Current/power regulated power supplies and PerkinElmer lamp housing units are recommended.
- 4. Lamp must be operated within recommended current and power range. Over powering may lead to arc instability, hard starting and premature aging.
- 5. CERMAX lamps are much safer lamps to use than their quartz xenon arc lamp equivalents. However, caution must be practiced when operating lamps because they are under high pressure, require high voltage, reach temperatures up to 200° C, and their IR and UV radiation can cause skin burns and eye damage. Read hazard sheet included with each lamp shipment.

Spectral Output



PerkinElmer welcomes inquiries about special lamps. We would be pleased to discuss the requirements of your application and the feasibility of designing a lamp specifically suited to your needs.

For more information e-mail us at opto@perkinelmer.com or visit our web site at www.perkinelmer.com/opto. All values are nominal; specifications subject to change without notice.

USA: PerkinElmer Optoelectronics 44370 Christy St. Fremont, CA 94538 Phone: (510) 979-6500 Fax: (510) 687-1140 Toll Free: (800) 775-6786 Europe: PerkinElmer Optoelectronics GmbH Wenzel-Jaksch-Str. 31 65199 Wiesbaden Germany Phone: +49 611 492 0 Fax: +49 611 492 369 Asia: PerkinElmer Optoelectronics 47 Ayer Rajah Crescent #06-12 Singapore 139947 Phone: +65 775 2022 Fax: +65 775 1008



DS-163 Rev C 1101

© 2000 PerkinElmer inc. All rights reserved.

www.perkinelmer.com/opto