

Vishay Telefunken



Silicon NPN Phototransistor

Description

BPX43 is a very high sensitive silicon NPN epitaxial planar phototransistor in a standard TO–18 hermetically sealed metal case with a glass lens.

A superior linearity of photocurrent vs. irradiation makes it ideal for linear applications. A base terminal is available to enable biasing and sensitivity control.

Features

- Hermetically sealed TO-18 case
- Lens window
- Angle of half sensitivity $\varphi = \pm 15^{\circ}$
- Exact central chip alignment
- Base terminal available
- Very high photo sensitivity
- High linearity
- Suitable for visible and near infrared radiation
- Selected into sensitivity groups


Applications

Detector for analogue and digital applications in industrial electronics, measuring and control, e.g. long range light barriers with additional optics, optical switches, alarm systems.

Absolute Maximum Ratings

 $T_{amb} = 25^{\circ}C$

Parameter	Test Conditions	Symbol	Value	Unit
Collector Base Voltage		V _{CBO}	80	V
Collector Emitter Voltage		V _{CEO}	70	V
Emitter Base Voltage		V _{EBO}	7	V
Collector Current		Ι _C	50	mA
Peak Collector Current	$t_p \leq 10 \ \mu s$	I _{CM}	200	mA
Total Power Dissipation	$T_{amb} \leq 25 \ ^{\circ}C$	P _{tot}	250	mW
Junction Temperature		Τ _i	125	°C
Operating Temperature Range		T _{op}	-55+125	°C
Storage Temperature Range		T _{stg}	-55+125	°C
Soldering Temperature	$t \leq 5$ s, distance from touching border ≥ 2 mm	T _{sd}	260	°C
Thermal Resistance Junction/Ambient		R _{thJA}	400	K/W
Thermal Resistance Junction/Case		R _{thJC}	150	K/W



Vishay Telefunken



Basic Characteristics

$T_{amb} = 25^{\circ}C$

Parameter	Test Conditions	Symbol	Min	Тур	Max	Unit
Collector Emitter Breakdown Voltage	I _C = 1 mA	V _{(BR)CE}	70			V
Collector Dark Current	$V_{CE} = 25 \text{ V}, \text{ E} = 0$	I _{CEO}		10	200	nA
Collector Emitter Capacitance	V _{CE} = 0 V, f = 1 MHz, E = 0	C _{CEO}		23		рF
Emitter Base Capacitance	V _{EB} = 0 V, f = 1 MHz, E = 0	C _{EBO}		47		рF
Collector Base Capacitance	$V_{CB} = 0 V, f = 1 MHz, E = 0$	C _{CBO}		41		рF
Collector Light Current	$E_e = 0.5 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}, V_{CE} = 5 \text{ V}$	I _{ca}	0.8			mA
Temp. Coefficient of I _{ca}	$\lambda = 950 \text{ nm}$	TK _{lca}		1		%/K
Base Light Current	$E_e = 0.5 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$, $V_{CB} = 5 \text{ V}$	I _{ba}		10		μΑ
Angle of Half Sensitivity		φ		±15		deg
Wavelength of Peak Sensitivity		λρ		920		nm
Range of Spectral Bandwidth		λ _{0.5}		6301040		nm
Collector Emitter Saturation Voltage	$E_e = 0.5 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$, $I_C = 0.1 \text{ mA}$	V _{CEsat}		0.15	0.3	V

Type Dedicated Characteristics

 $T_{amb} = 25^{\circ}C$


Parameter	Test Conditions	Туре	Symbol	Min	Тур	Max	Unit
	V_{CE} = 5 V, I_{C} = 1 mA	BPX38–4	В		330		
		BPX38–5	В		520		
		BPX38–6	В		650		
Collector Light Current E_{ϵ}	E_e =0.5 mW/cm ² , λ =950nm, V _{CE} =5V	BPX38–4	I _{ca}	0.5	0.7	1.0	mA
		BPX38–5	I _{ca}	0.8	1.25	1.6	mA
		BPX38–6	I _{ca}	1.25	2		mA
	V _{CE} =5V, I _C =1mA, R _L =1kΩ λ =820nm	BPX38–4	t _r , t _f		15		μs
		BPX38–5	t _r , t _f		20		μs
		BPX38–6	t _r , t _f		25		μs




BPX43

Vishay Telefunken

Typical Characteristics ($T_{amb} = 25^{\circ}C$ unless otherwise specified)








Figure 4. Collector Light Current vs. Irradiance




Figure 5. Collector Light Current vs. Collector Emitter Voltage







Figure 6. Amplification vs. Collector Current


Document Number 81534 Rev. 2, 20-May-99 BPX43 Vishay Telefunken














Figure 9. Collector Emitter Capacitance vs. Collector Emitter Voltage




Figure 10. Relative Spectral Sensitivity vs. Wavelength





Figure 11. Relative Radiant Sensitivity vs. Angular Displacement



Dimensions in mm



96 12178



technical drawings according to DIN specifications

BPX43

Vishay Telefunken



Ozone Depleting Substances Policy Statement

It is the policy of Vishay Semiconductor GmbH to

- 1. Meet all present and future national and international statutory requirements.
- 2. Regularly and continuously improve the performance of our products, processes, distribution and operating systems with respect to their impact on the health and safety of our employees and the public, as well as their impact on the environment.

It is particular concern to control or eliminate releases of those substances into the atmosphere which are known as ozone depleting substances (ODSs).

The Montreal Protocol (1987) and its London Amendments (1990) intend to severely restrict the use of ODSs and forbid their use within the next ten years. Various national and international initiatives are pressing for an earlier ban on these substances.

Vishay Semiconductor GmbH has been able to use its policy of continuous improvements to eliminate the use of ODSs listed in the following documents.

- 1. Annex A, B and list of transitional substances of the Montreal Protocol and the London Amendments respectively
- 2. Class I and II ozone depleting substances in the Clean Air Act Amendments of 1990 by the Environmental Protection Agency (EPA) in the USA
- 3. Council Decision 88/540/EEC and 91/690/EEC Annex A, B and C (transitional substances) respectively.

Vishay Semiconductor GmbH can certify that our semiconductors are not manufactured with ozone depleting substances and do not contain such substances.

We reserve the right to make changes to improve technical design and may do so without further notice. Parameters can vary in different applications. All operating parameters must be validated for each customer application by the customer. Should the buyer use Vishay-Telefunken products for any unintended or unauthorized application, the buyer shall indemnify Vishay-Telefunken against all claims, costs, damages, and expenses, arising out of, directly or indirectly, any claim of personal damage, injury or death associated with such unintended or unauthorized use.

> Vishay Semiconductor GmbH, P.O.B. 3535, D-74025 Heilbronn, Germany Telephone: 49 (0)7131 67 2831, Fax number: 49 (0)7131 67 2423